

# Distributeurs Verson Vlies Courcier Sarl

**VVC**.rr ZA des Wattines, 5 Pavé d'Halluin

F-59126 LINSELLES

T: 03.20.46.59.66 F: 03.20.03.17.38

info@vvc.fr



## **GINTRONIC IDC-6**

## Made in Switzerland


The JIS L1099 B1 + B2 is one of the most common standards for measuring the Moisture Vapour Transmission Rate of fabrics and textiles, especially for the outdoor market. GINTRONIC IDC-6 is offering for this a state of the art tester, with automatic temperature control of the waterbath AND the ambient temperature. With the IDC-6 you can measure 6 samples at the same time.

The GINTRONIC IDC-6 also conforms to ISO 15496.



ZA des Wattines, 5 Pavé d'Halluin F-59126 LINSELLES T: 03.20.46.59.66 F: 03.20.03.17.38

info@vvc.fr



### **GINTRONIC IDC-6**

## Inverted drycup WVTR Tester:

For the determination of the water vapour transmission rates of fabrics, foils, films and other sheet materials based on the gravimetric inverted drycup method.

Conforms to JIS L1099 B1 + B2 (Method A1 and A2 are not supported - for this the GINTRONIC Gravi-Test is recommended).

#### Microprocessor controlled

Integrated temperature control: selfcooling of the testchamber up to 3°C below ambient temperature Integrated temperature control: selfheating of the testchamber up to 40°C

Integrated humidity control: testchamber is maintained below a user pre-defined value (20-60%r.H.) Integrated temperature control: selfheating and cooling of the waterbath from -7°C to 0°C below the setpoint of the temperated chamber.

Easy and userfriendly input of the temperatures via integrated Touchscreen.

Automatic controll of the water level of the watherbath.

Compressed Air with 6 bar needed. Voltage: 230 VAC or 115/110 VAC. Dimensions: approx. 700 x 650 mm Weight without PC: approx. 55 kg

All specifications are related to a room with an ambient temperature of 23 +/-  $1^{\circ}$ C and a relative humidity of 50 +/- $5^{\circ}$ r.H.

Subject to modifications in the interest of technical progress. Device conforms to valid CE-norms.

GINTRONIC AG
Holunderweg 10
CH-8704 Herrliberg
Telefon 0041 55 260 34 66
Telefax 0041 55 260 34 67
www.gintronic-instruments.com
info@gintronic-instruments.com